



PRODUCT-DETAILS

TY125-18

CABLE TIE 18LB 5IN NATURAL NYLON



General Information

Extended Product Type	TY125-18
Product ID	7TCG054360R0104
EAN	5414363060413
Catalog Description	CABLE TIE 18LB 5IN NATURAL NYLON
Long Description	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 142mm (5.59 Inches), Width of 2.5mm (0.10 Inches), Thickness of 1.2mm (0.05 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds), Bulk Pack

Ordering

EAN	5414363060413
Customs Tariff Number	3926909990

Dimensions

Product Net Weight	.001 lb .454 g
--------------------	-------------------

Container Information

Package Level 1 Units	1000 piece
Package Level 1 Width	2 in 51 mm

Package Level 1 Height	12 in 305 mm
Package Level 1 Depth / Length	14 in 356 mm
Package Level 2 Units	10000 piece
Package Level 2 Width	10.8 in 274 mm
Package Level 2 Height	10.9 in 277 mm
Package Level 2 Depth / Length	13.2 in 335 mm

Additional Information

Brand / Label	Ty-Fast
Bundle Diameter	0.06 to 1.26 in 1.6 to 32 mm
Color	Natural
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	NYLON CABLE TIE
Product Type	General Purpose
Special Functions	The integrally formed nylon pawl combines low insertion and high locking strength.
Standards	UL E49405
Tensile Strength	18 lb 80 N
Thickness	0.05 in 1.2 mm
UPC	786210231037

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY125-18
Declaration of Conformity - CE	9AKK107492A9843
Instructions and Manuals	TY125-18

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

