

CP879 pneumatic angle drill

200 watt



Application:

For drilling boreholes in poorly accessible places.

Execution:

- With clockwise and anti-clockwise rotation
- With sensitive valve control

Delivery:

In cardboard box



Art. no.	75032 110
Model	CP879
Max. drilling diameter in steel	10 mm
Max. idle speed	1800 rpm
Power output	370 W
Air consumption	480 l/min
Connection thread	G 1/4 inch
Min./max. drill chuck span width	1-10 mm
Inner hose diameter	10 mm
Weight	1 kg
With right/left-hand rotation	Yes
Product Group	Prod. Gr. 752

EAN

0015451394912