

GH195, FC310, GH663, 2781, SH222-16

Fittings
High Pressure

Hochdruck-
armaturen

Embouts
haute pression

Raccordi
alta pressione

Racores
altas pressione

50


DKOL Female
Swivel/O-Ring,
Light Duty

DKOL
Dichtkopf/O-Ring,
leichte Baureihe

DKOL avec joint
torique, série L

Femmina girevole
DKOL/O-Ring,
serie leggera

Hembra loca
DKOL con anillo
en O, serie ligera



Part Number	Thread T	Flange	Tube O.D. mm	Hose ND	Hose Size	A mm	D mm	H mm	E Ø mm	K Ø mm	R Ø mm	HEX [1]	HEX [2]	Nut
GAI0933-4	M14x1,5		8	6	-4	65	34		4			17	17	
GAI7568-6	M16x1,5		10	10	-6	72	36		4			19	19	
GAI0933-6	M18x1,5		12	10	-6	73	36		8			22	22	
GAI0933-8	M22x1,5		15	12	-8	77	40		10			27	27	
GAI0933-10	M26x1,5		18	16	-10	81	43		13			32	32	
GAI0933-12	M30x2,0		22	19	-12	93	46		16			36	32	
GAI0933-16	M36x2,0		28	25	-16	106	55		21			41	41	
GAI0933-20	M45x2,0		35	31	-20	118	60		27			50	50	


DKOL Female
Swivel/O-Ring,
Light Duty, 45°
Elbow

DKOL
Dichtkopf/O-Ring,
leichte Baureihe,
45° Krümmer

DKOL avec joint
torique, série L
coudé 45°

Femmina girevole
DKOL/O-Ring a
45°, serie leggera

Hembra loca
DKOL acodado a
45° con anillo en
O, serie ligera



Part Number	Thread T	Flange	Tube O.D. mm	Hose ND	Hose Size	A mm	D mm	H mm	E Ø mm	K Ø mm	R Ø mm	HEX [1]	HEX [2]	Nut
GAI7537-4	M14x1,5		8	6	-4	73	42	14	4			17	14	
GAI7571-6	M16x1,5		10	10	-6	84	48	17	7			19	17	
GAI7537-6	M18x1,5		12	10	-6	84	47	17	8			22	17	
GAI7537-8	M22x1,5		15	12	-8	90	53	18	10			27	19	
GAI7537-10	M26x1,5		18	16	-10	106	68	25	13			32	22	
GAI7537-12	M30x2,0		22	19	-12	108	61	21	16			36	27	
GAI7537-16	M36x2,0		28	25	-16	130	79	25	20,5			41	32	


DKOL Female
Swivel/O-Ring,
Light Duty, 90°
Elbow

DKOL
Dichtkopf/O-Ring,
leichte Baureihe,
90° Krümmer

DKOL avec joint
torique, série L
coudé 90°

Femmina girevole
DKOL/O-Ring a
90°, serie leggera

Hembra loca
DKOL acodado a
90° con anillo en
O, serie ligera



Part Number	Thread T	Flange	Tube O.D. mm	Hose ND	Hose Size	A mm	D mm	H mm	E Ø mm	K Ø mm	R Ø mm	HEX [1]	HEX [2]	Nut
GAI7544-4	M14x1,5		8	6	-4	66	35	28	4			17	14	
GAI5063-6	M16x1,5		10	10	-6	75	38	35	8			19	17	
GAI7544-6	M18x1,5		12	10	-6	78	41	35	8			22	17	
GAI7544-8	M22x1,5		15	12	-8	85	47	38	10			27	19	
GAI7544-10	M26x1,5		18	16	-10	100	63	53	13			32	22	
GAI7544-12	M30x2,0		22	19	-12	105	58	47	16			36	27	
GAI7544-16	M36x2,0		28	25	-16	129	77	59	21			41	32	