



Order code	Dimensions (mm)				Wire size	
	L	D	D1	D2	AWG	DIM mm <sup>2</sup>
<b>31-1130</b>	10	1.0	1.3	2.1	#22	0.50
<b>31-1131</b>	10	1.2	1.5	2.3	#20	0.75
<b>31-1132</b>	10	1.4	1.7	2.5	#18	1.00
<b>31-1133</b>	10	1.7	2.0	2.8	#16	1.50
<b>31-1134</b>	10	2.2	2.5	3.4	#14	2.50
<b>33-1135</b>	12	2.8	3.2	4.0	#12	4.00
<b>33-1136</b>	15	3.5	3.9	4.7	#10	6.00
<b>33-1137</b>	18	4.5	4.9	5.8	#8	10.00
<b>33-1138</b>	15	5.8	6.2	7.5	#6	16.00
<b>33-1139</b>	16	7.3	7.7	9.5	#4	25.00