


## LED-INDICATOR BLUE


LED 10mm - 24V DC - 20 mA - IP67

(blue)  
24 V DC

### [Link to Product](#)

#### Illustration





Product may differ from Image

### Technical Data

Operating voltage	24 V DC $\pm 15\%$
Current consumption	approx. 15 mA
Protection acc. to (IEC 60529/EN 60529)	IP67

### General data

Housing	Brass, chrome plated
LED $\varnothing$	10 mm
Front panel hole diameter $\varnothing$	14 mm
Dimensions H $\times$ W $\times$ D	16 $\times$ 16 $\times$ 45 mm
Temperature range	-40...+70 °C
Connection	Faston 2.8 $\times$ 0.8 mm

### Commercial data

country of origin	DE
customs tariff number	85414010
minimum order quantity	10