


entrelec

terminal blocks

clamp
DIN 1 - 3

M 16/12...

Spacing 12 mm - 0,1 (.473")



center of rail

Standard 12 mm block with partition.

0115 129.14

149-298

Standard blocks

Grey	M 16/12	0115 129.14
Blue	M 16/12.N	0125 129.16
Yellow	M 16/12	0105 129.23
Beige V0	M 16/12.V0	0195 129.15
Blue V0	M 16/12.N.V0	0199 005.21

Accessories

1	End section	grey	FEM12	th. 3,0 mm	0118 618.01
		blue	FEM12	th. 3,0 mm	0128 618.03
		yellow	FEM12	th. 3,0 mm	0103 065.24
		beige	FEM12 V0	th. 3,0 mm	0188 618.02
		blue	FEM12 V0	th. 3,0 mm	0199 303.00
2	Separator end section	grey	SCF12	th. 3,0 mm	0119 102.10
		beige	SCF12 V0	th. 3,0 mm	0193 102.11
3	Separator end section	grey	SCFM6	th. 3,0 mm	0114 825.05
4	Separator end section	grey	SCFEX1	th. 2,4 mm	0109 619.04
5	Separator end section	grey	SCFEX3	th. 2,4 mm	0103 620.01
6	Separator end section for cover CPV	grey	SCFCV 1.2	th. 2,0 mm	0118 795.11
		beige	SCFCV 1.2 V0 V0	th. 2,0 mm	0196 765.12
7	Protective cover		CPM	(for SCF12... SCFM6)	0187 312.14
8	Protective cover		CPV 1.2	(for SCFCV 1.2)	0118 810.12
9	Test socket		AL2	DIA. 2,0 mm	0163 043.21
			AL3	DIA. 3,0 mm	0163 261.00
			AL4	DIA. 4,0 mm	0163 262.01
10	Test plug		FC2	DIA. 2,0 mm	0197 885.28
			FC4	DIA. 4,0 mm	0197 890.01
11	Assembled jumper bar	76 A	BJM 12	2 poles	0179 618.16
		76 A	BJM 12	3 poles	0179 619.17
					0179 620.14