

PRODUCT SPECIFICATION

**Carl
Kammerling**
International

Brand	C.K
Product Range	Dextro VDE Stubby Slim Screwdrivers
Catalogue number	48343, 48344, 48345
Date	26/01/2018

Range Description

A range of slim-shafted VDE approved professional electricians' stubby screwdrivers

Features

- Slim shafted insulated blades - allow access to recessed screws and fixings
- Cellulose acetate handles – shatterproof and wipe clean
- Non-roll handle design – specifically designed to stop the screwdrivers rolling off non-flat surfaces
- Tip type marking on the end of the handle for convenient blade type identification
- Toughened high alloy steel blade offering the ultimate in wear resistance and performance
- Molybdenum-vanadium-steel blade with black non-peel tip finish for corrosion protection
- Precision machined tips for the ultimate screw fit and high torque output



T48343-2



T48344-040



T48344-055



T48345-2



T48349

Item Number	Item Description	EAN No	Commodity code	Carton Qty
T48343-2	Stubby VDE Slim Screwdriver PZ2x46	5013969960921	8205400000	6
T48344-040	Stubby VDE Slim Screwdriver SL4.0x46	5013969960952	8205400000	6
T48344-055	Stubby VDE Slim Screwdriver SL5.5x46	5013969960969	8205400000	6

T48345-2	Stubby VDE Slim Screwdriver MOD2x46	5013969960976	8205400000	6
300004	Stubby VDE Slim Screwdriver Stand	N/A	73262000	1
T49398H	Stubby VDE Slim Screwdriver Stand Header	N/A	49111090	1
T48349	Stubby VDE Slim Screwdriver Set/4	5013969244595	82054000	20

<p>Technical product information</p>	<p>Blade/Shaft</p> <p>Made from chrome molybdenum vanadium steel, hardened to 57-59 HRC, black non-peel finish.</p> <p>Handle</p> <p>The handle core is polypropylene, injection moulded around the blade with a TPE soft grip over-mould. The handles are shatterproof down to -35° C.</p> <p>Dimensions</p> <table border="1" data-bbox="488 779 1252 995"> <thead> <tr> <th>Dimensions (mm)</th> <th>Handle length</th> <th>Blade length</th> <th>Blade Dia</th> <th>Tip thickness</th> </tr> </thead> <tbody> <tr> <td>T48343-2</td> <td>60</td> <td>46</td> <td>6.0</td> <td>-</td> </tr> <tr> <td>T48344-040</td> <td>60</td> <td>46</td> <td>4.0</td> <td>0.8</td> </tr> <tr> <td>T48344-055</td> <td>60</td> <td>46</td> <td>5.5</td> <td>1.0</td> </tr> <tr> <td>T48345-2</td> <td>60</td> <td>46</td> <td>6.0</td> <td>-</td> </tr> </tbody> </table>	Dimensions (mm)	Handle length	Blade length	Blade Dia	Tip thickness	T48343-2	60	46	6.0	-	T48344-040	60	46	4.0	0.8	T48344-055	60	46	5.5	1.0	T48345-2	60	46	6.0	-
Dimensions (mm)	Handle length	Blade length	Blade Dia	Tip thickness																						
T48343-2	60	46	6.0	-																						
T48344-040	60	46	4.0	0.8																						
T48344-055	60	46	5.5	1.0																						
T48345-2	60	46	6.0	-																						
<p>Standards compliance</p>	<p>Electrical safety</p> <p>Fully approved and independently audited by the German VDE institute to VDE 0682/201:2005 01 IEC 60900:2012</p> <p>Dimensional and performance</p> <p>Slotted screwdrivers – DIN ISO 2380 PZD/SDV/PH Screwdrivers – DIN ISO 8764</p>																									
<p>User health and safety information</p>	<p>Users and bystanders are advised to wear safety goggles</p>																									
<p>RoHS/WEEE compliance</p>	<p>This product range does not fall within the scope of RoHS or WEEE regulations</p>																									
<p>Material safety data</p>	<p>None applicable</p>																									
<p>Warranty</p>	<p>Dextro Screwdrivers are guaranteed for life against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not covered</p>																									
<p>Country of origin</p>	<p>Germany</p>																									

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T48343-2	35	35	106	53	35	35	106	53
T48344-040	35	35	106	50	35	35	106	51
T48344-055	35	35	106	51	35	35	106	51
T48345-2	35	35	106	53	35	35	106	53
300004	160	250	245	2700	160	250	245	2700
T49398H	146	3	155	30	146	3	155	30
T48349	150	35	165	235	150	35	165	235

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Length mm	Width mm	Depth mm	Gross weight g	No of cartons on base	Number of rows high
T48343-2	200	80	60	53g	6	4
T48344-040	200	80	60	53g	6	4
T48344-055	200	80	60	53g	6	4
T48345-2	200	80	60	53g	6	4
T48349	320	230	200	4950	30	5

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T48343-2	-	-	-	-	-	-	200	Box
T48344-040	-	-	-	-	-	-	200	Box
T48344-055	-	-	-	-	-	-	200	Box
T48345-2	-	-	-	-	-	-	200	Box
T48349	15	Hanger	-	-	-	-	250	Box