

Product data sheet

Item No. 91.222.1060.9

Cable assembly GST15i2KSBS 15HW 10PB01

geis® Extension cable female - male; length: 1m; type GST15i2; 2-pole; 250 V / 16 A; colour of coding: pastel blue with white strain-relief; cable: H05Z1Z1-F 2x1,5, colour: white



Item No.	91.222.1060.9
EAN	4015573924871
Order Unit	100 Piece(s)

Certificates / Approvals

Technical data

General

Rated current	6 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	2
Mechanical coding	Yes
Interlockable	Yes
Color of coding/ contact carrier	Pastel blue
Marking of poles	
Color of housing inclusive strain relief	White

Model

Number of poles	2
Nominal cross section conductor	1.5 mm ²
Degree of protection (IP)	IP40
Cable type	S05HH-F
Cable colour	White
Cable diameter	7.5 mm
Version of cable	Female - male
Type of cord set	Connecting cable
Version cable end 1	GST15i2 socket

Version cable end 2	GST15i2 plug
---------------------	--------------

Material

Surface finish	Silver-plated
Halogen free	Yes
Continuous temperature of cable	70 °C
Insulation components continuous temperature	100 °C

Dimensions

Total length	1 m
--------------	-----