

## Pneumatic straight grinder G 804 D

**MANNESMANN  
DEMAG**

### Application:

Specially designed for fine milling, grinding, engraving and polishing work

### Version:

- Ergonomic design
- Rear exhaust via hose unit with integrated silencer
- With elastic spindle bearings and spindle cap

### Delivery:

Includes hose unit and collet chuck keys



<b>Art. no.</b>	<b>75061 050</b>
<b>Valve design</b>	Rotary valve
<b>Max. idle speed</b>	80000 rpm
<b>Min./max. idle speed</b>	0-80000 rpm
<b>Power output</b>	110 W
<b>Air consumption</b>	3 l/s
<b>Sound-pressure level</b>	74 dB
<b>Length</b>	113 mm
<b>Diameter of housing</b>	20 mm
<b>Collet chuck diameter</b>	3 mm
<b>Suitable for max. sanding block diameter</b>	6 mm
<b>Max. HM rotating milling cutter diameter</b>	4 mm
<b>Weight</b>	0.21 kg

### EAN-Code

4251757301865