



## KEY FEATURES

---

Höhe der Anschlussplatte 400 mm

Schwenkhebelgriff mit Druckknopf

Öffnungswinkel 180°

Stahltür mit 5-Punkt-Verriegelung für EMV-Anwendungen

## PRODUKTMERKMALE

---

Produkttyp: Schranktür

Produktfamilie: Varistar CP

Verschlussart: 4-Punkt-Verriegelung

Farbe: Schwarzgrau

Farbecode: RAL 7021

Höhe: 47 HE

Höhe: 2200 mm

Breite (mm): 800 mm

Schutzart: IP55

## ZUSÄTZLICHE PRODUKTDDETAILS

---

EMV- und IP55 Stahltür mit Schwenkhebelgriff und 5-Punkt-Verriegelung.

Bitte bestellen Sie den Erdungssatz separat.

### **Nordamerika**

All locations

+1.763.422.2661

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)

### **Europa**

Straubenhardt, Deutschland

+49.7082.794.0

Betschdorf, Frankreich

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)

### **Asia**

Shanghai, China

+86.21.2412.6943

Qingdao, Volksrepublik

China

+86.532.8771.6101

Singapur

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)

### **Middle East & India**

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, Indien

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2024 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.