



13	742300	Hexagon socket head cap screw ISO 4762-M4x14	4	3	-	2,2
12	9400029901	Han HPR HPTC coding-element	2			
11	9110026235	Han HPR HPTC 850/1400-fe.-cont.-150mm <sup>2</sup>	1			
10	19400020810_03	Han HPR HPTC 850/1400 CS-HB-c.-retainer	1			
9	19400020810_02	Han HPR HPTC 850 CS-cover-insul.-body	1			
8	19400020810_01	Han HPR HPTC 850/1400 CS-HB-insul.-body	1			
7	19400020800_11	Han HPR HPTC 850 CS-Cover	1			
6	19000007126	Han CGM-M-Rail M40 D.21-26.5mm	1	46	50	20,0
5	19400020890_05	O-Ring	1			
4	19400020890_06	O-Ring	2			
3	743400	Lock washer	2			
2	742900	Hexagon socket head cap screw ISO 4762-M8x35	2	6	-	14,5
1	19400020808_50	Han HPR HPTC 850/1400 CS-HB-M40	1			
item	partnumber	partname	QTY	SW1	SW2	tightening torque Nm

parts in scope of delivery are not assembled  
 assembly instruction enclosed  
 crimp zone acc. to DIN EN 46235, indicator 22  
 for stranded fine wire acc to VDE 0295 class 5/ IEC 60228 class 5  
 wire gauge: 150mm<sup>2</sup>

Coating	A=	mm <sup>2</sup>	V=	mm <sup>3</sup>	m=	g	Mat.
	All Dimensions in mm Original Size DIN A3	Scale 1:2	Free size tol.	Ref.			
	All rights reserved Department EL PD	Created by MEYERLE	Inspected by 00103912	Standardisation	Date 2021-10-04	State Final Release	
	HARTING D-32339 Espelkamp	Title Han HPR HPTC 850 CS UNSH IP65/67 150			Doc-Key / ECM-Nr. 100941836/UGD/002/D 50000203563		
	Type TB	Number 10 40 281 2117			Rev. D	Page 1/1	

