




DIN 84 A

~ISO 1207

Norm zurückgezogen



BN 650

Zylinderschrauben

mit Schlitz

INOX A2

- ~UNI 6107
- ~ČSN 021131

[3D Cadenas](#)

Alle Längen Gewinde ~ bis Kopf

Article#	d ₁	d ₂	k	n	t min.	L
1421611	M1	2	0,7	0,25	0,25	2
1421638						3
1421646						4
1072730						5
1072749						6
1072757						8
1072765						10
1421654	M1,2	2,3	0,8	0,3	0,3	2
1421662						3
1421670						4
1421689						5
1072773						6
1072781						8
1072803						10
1421697	M1,4	2,6	0,9	0,3	0,4	3
1421700						4
1421719						5
1421727						6
1072870						8
1072897						10
1210165	M1,6	3	1	0,4	0,45	2
1243683						3
1243691						4
1243705						5
1243713						6
1243721						8

Article#	d ₁	d ₂	k	n	t min.	L
1243748	M1,6	3	1	0,4	0,45	10
1243756						12
1243764						(14)
1243772						16
1114255	M2	3,8	1,3	0,5	0,6	3
1243780						4
1243799						5
1243802						6
1243810						8
1243829						10
1243837						12
1243845						(14)
1243853						16
1114263						20
1425374						25
1114271	M2,5	4,5	1,6	0,6	0,7	3
1243861						4
1243888						5
1243896						6
1243918						8
1243926						10
1243934						12
1243942						(14)
1243950						16
1243969						20
1114298						25
8184372						30
1243977	(M2,6)	5	1,7	0,6	0,8	4
1243985						5
1243993						6
1244000						8
1244019						10
1244027						12
1114328	M3	5,5	2	0,8	0,85	3
1244043						4
1244051						5
1244078						6
1244094						8
1244108						10
1244116						12
1244124						(14)

Article#	d ₁	d ₂	k	n	t min.	L
1244132	M3	5,5	2	0,8	0,85	16
1425382						(18)
1244140						20
1570366						(22)
1244159						25
1421735						30
1114336						35
1072951						40
1210173						45
1114344						50
5514692						55
3059863						60
1570374	(M3,5)	6	2,4	1	1	5
1244167						6
1244175						8
1244183						10
1244191						12
1244205						16
1210181						20
1210203						25
1210211						30
1570382						40
1210238	M4	7	2,6	1,2	1,1	4
1244213						5
1244221						6
1244248						8
1244256						10
1244264						12
1244272						(14)
1244280						16
1244299						(18)
1244302						20
1570390						(22)
1244310						25
1244329						30
1244337						35
1244345						40
1210246						45
1114352						50
1210254						55
1210262						60

Article#	d ₁	d ₂	k	n	t min.	L
1570412	M4	7	2,6	1,2	1,1	70
1570420						80
5522168						100
1244353	M5	8,5	3,3	1,2	1,3	6
1244361						8
1244388						10
1244396						12
1244418						(14)
1244426						16
1244434						(18)
1244442						20
1244450						25
1244469						30
1244477						35
1244485						40
1114360						45
1072978						50
1244493						60
1244507						70
1072986						80
1210289						90
1210297						100
1244515	M6	10	3,9	1,6	1,6	8
1244523						10
1244531						12
1244558						(14)
1244566						16
1570439						(18)
1244574						20
1244582						25
1244590						30
1421743						35
1244604						40
1114379						45
1421751						50
1114387						60
1244612						70
1244620						80
1210300						90
1210319						100
1570447	M8	13	5	2	2	10

Article#	d ₁	d ₂	k	n	t min.	L
1425390	M8	13	5	2	2	12
1244639						(14)
1244647						16
1244655						20
1244663						25
1244671						30
1425404						35
1244698						40
1114395						45
1421778						50
1114409						60
1425412						70
1425420						80
1425439						90
1425447						100