



Sample photo

Order symbol: PC 21/18-C3
Product nbr: 7520081
Description: Enclosure, PC
Remarks: Without main cover

EAN: 6418074010216
EI. number:
 Finland: 3422928
 Electric No. 8212016619
 Denmark:
 Electric No. Italy: 7719002
 Electric No. Sweden: 7520081

Including: Base, terminal compartment cover with PUR gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Dimensions:	Length	Width	Height	Accessories:
mm:	213	185	90	FP 21/18 Front plate (aluminium) FC PC 21/18 Frame of PC front plate
inch:	8.4	7.3	3.5	
Materials:				Rating:
Material:	Polycarbonate			Impact Resistance (EN 62262): IK07
Base colour:	RAL 7035 -light grey			Electrical insulation: Totally insulated
Gasket material:	EPDM			Halogen free (DIN/VDE 0472, Part 815): 1
Temperatures:				UV resistance: UL 508
Temperature °C (short term):	-40 ... 120 °C			Flammability Rating: UL 746C 5V
Temperature °C (continuous):	-40 ... 80 °C			Glow Wire Test (IEC 695-2-1) °C: 960
Temperature °F (short term):	-40 ... 250 °F			NEMA Class: NEMA 1, 3, 3R, 12, 13
Temperature °F (continuous):	-40 ... 175 °F			Certificates:
Accessories:				SGS Fimko
MP 21/18	Mounting plate			Gost R

