


PUSH ON TERMINALS (INSULATED AND NON INSULATED)



Female

Vinyl insulated



Part Number	Conductor Size mm ²	To Suit width mm	Colour
DVP01-2.8F5	0.25-1.65	2.8 x 0.5	Red
DVP01-2.8F8	0.25-1.65	2.8 x 0.8	Red
DVP01-4.8F5	0.25-1.65	4.8 x 0.5	Red
DVP01-4.8F8	0.25-1.65	4.8 x 0.8	Red
DVP01-6.3F	0.25-1.65	6.3	Red
DVP02-4.8F5	1.04-2.63	4.8 x 0.5	Blue
DVP02-4.8F8	1.04-2.63	4.8 x 0.8	Blue
DVP02-6.3F	1.04-2.63	6.3	Blue
DVP02-8.0F	1.04-2.63	8.0 x 0.8	Blue
DVP05-6.3F	2.63-6.64	6.3	Yellow
DVP05-9.5F	2.63-6.64	9.5	Yellow

Suitable crimping tools:

Red: DHC 15, DHC 15Y, DHCR 1, DHCR 15, DBMT 1, 3 & 4

Blue: DHC 15, DHC 15Y, DHCR 2, DHCR 15, DBMT 1, 3 & 4

Yellow: DHC 15, DHC 15Y, DHCR 5, DHCR 15, DBMT 1, 3 & 4

Female

Vinyl insulated



Part Number	Conductor Size mm ²	To Suit width mm	Colour
*DNFP01-2.8F5	0.25-1.65	2.8 x 0.5	Red
*DNFP01-2.8F8	0.25-1.65	2.8 x 0.8	Red
DVFP01-4.8F5	0.25-1.65	4.8 x 0.5	Red
DVFP01-4.8F8	0.25-1.65	4.8 x 0.8	Red
DVFP01-6.3F	0.25-1.65	6.3	Red
DVFP02-4.8F5	1.04-2.63	4.8 x 0.5	Blue
DVFP02-4.8F8	1.04-2.63	4.8	Blue
DVFP02-6.3F	1.04-2.63	6.3	Blue
DVFP05-6.3F	2.63-6.64	6.3	Yellow
DVFP05-9.5F	2.63-6.64	6.3	Yellow

*DNFP0 Nylon Insulated

Female

Part Number	Conductor Size mm ²	To Suit width mm
DP01-2.8F5	0.25 1.65	2.8 x 0.5
DP01-2.8F8	0.25 1.65	2.8 x 0.8
DP01-4.8F5	0.25 1.65	4.8 x 0.5
DP01-4.8F8	0.25 1.65	4.8 x 0.8
DP01-6.3F	0.25 1.65	6.3
DP02-4.8F5	1.04 2.63	4.8 x 0.5
DP02-4.8F8	1 04 2.63	4.8 x 0.8
DP02-6.3F	1.04 2.63	6.3
DP05-6.3F	2.63 6.64	6.3
DP05-9.5F	2.63 6.64	9.5

Suitable crimping tools:

DHCF 15, DHCRF 15, DBMT 1, 3 & 4.

Male

Vinyl insulated



Part Number	Dimensions mm	Conductor Size mm ²	Colour
	W T L		
DVPO 1-4.8M	4.75 0.8 9.5	0.25 x 1.65	Red
DVPO 1-6.3M	6.35 0.8 9.5	0.25 x 1.65	Red
DVPO 2-4.8M	4.75 0.8 9.5	1.04 x 2.63	Blue
DVPO 2-6.3M	6.35 0.8 9.5	1.04 x 2.63	Blue
DVPO 5 6.3M	6.35 0.8 9.5	2.63 x 6.64	Yellow

Suitable crimping tools:

Red: DHC 15, DHC 15Y, DHCR 1, DHCR 15, DBMT 1, 3 & 4

Blue: DHC 15, DHC 15Y, DHCR 2, DHCR 15, DBMT 1, 3 & 4

Yellow: DHC 15, DHC 15Y, DHCR5, DHCR 15, DBMT 1, 3 & 4

Male

Part Number	Dimensions mm	Conductor Size mm ²
	d D L	
DPO 1-4.8M	4.75 0.5 6.35	0.3-0.75
DPO 1-6.3M	6.35 0.8 9.5	0.5-2.0
DPO 2-6.3M	6.3 6.3 9.5	1.0-2.5

Suitable crimping tools:

DHCF 15, DHCRF 15, DBMT 1, 3 and 4