

Konverteringstabel Statoil til FUCHS Automotive

Statoil produkt	FUCHS produkt	Specifikationer	Godkendelser	FUCHS anbefalinger
MOTOROLIER TIL TUNGE KØRETØJER				
MaxWay 10W-40	TITAN TRUCK PLUS SAE 10W-40	ACEA E7 API CI-4/SL GLOBAL DHD-1 CAT ECF-1-a/ ECF-2	DEUTZ DQC III-10, MACK EO-N MAN M 3275-1, MB-APPROVAL 228.3, MTU DDC TYPE 2, RENAULT RLD-2, VOLVO VDS-3.	CUMMINS CES, 20076/20077/20078, Scania LDF-2.
MaxWay 10W-30	TITAN TRUCK PLUS SAE 10W-30	ACEA E7 API CI-4, API SL	Deutz DQC III-10, Volvo VDS-3 MTU Type 2, Mack EO-N Renault VI RLD-2.	MB-Approval 228.3, MAN M 3275-1, CES 20076, CES 20077, Deutz DQC III-10, CAT ECF-2 CES 20078.
MaxWay 15W-40 PowerWay 15W-40 (4L)	TITAN TRUCK PLUS SAE 15W-40	ACEA E7 API CI-4/SL GLOBAL DHD-1 CAT ECF-1-a/ ECF-2	CUMMINS CES 20076/7/8, DETROIT DIESEL 93K215, DEUTZ DQC III-10, MACK EO-N, MAN M 3275-1, MB-APPROVAL 228.3, MTU DDC TYPE 2, RENAULT RLD/RLD-2, VOLVO VDS-3.	ALLISON C-4, CAT TO-2, CASE MS 1121, CUMMINS CES 20071/2, IVECO 18-1804 CLASSE T2 E7, NH 330H.
MaxWay E9 10W-30	TITAN CARGO SAE 10W-30	ACEA E9 API CJ-4/SN CAT ECF1-a/ ECF-2/ECF-3	DEUTZ DQC III-10 LA, MACK EO-O PREMIUM PLUS, MAN M 3575, MB-APPROVAL 228.31, RENAULT RLD-3, VOLVO VDS-4.	CUMMINS CES 20081 MTU DDC TYPE 2.1.
MaxWay E9 15W-40	TITAN CARGO SAE 15W-40	ACEA E9 API CJ-4/CI-4 PLUS/CI-4/SM CAT ECF-2/ECF-3 JASO DH-2	CUMMINS CES 20081, DEUTZ DQC III-10 LA, DETROIT DIESEL 93K218, MACK EO-O PREMIUM PLUS, MAN M 3275-1, MAN M 3575, MB-APPROVAL 228.31, MTU DDC TYPE 2.1, RENAULT RLD-3, VOLVO VDS-4.	ALLISON C-4.
MaxWay Ultra 5W-30	TITAN CARGO SL SAE 5W-30	ACEA E7/E4	DEUTZ DQC IV-10, FORD WSS- M2C212-A1, MACK EO-N, MAN M 3277, MB-APPROVAL 228.5, MTU DDC TYPE 3, RENAULT RXD/RLD-2, SCANIA LDF-3, VOLVO VDS-3.	CUMMINS CES 20077, IVECO 18-1804 CLASSE TFE, SCANIA LDF-2.
MaxWay Ultra E4 10W-40	TITAN CARGO LD3 SAE 10W-40	ACEA E7/E4	MACK EO-N, MAN M 3277, MB-APPROVAL 228.5, RENAULT RLD-2, SCANIA LDF-3, VOLVO VDS-3.	API CF.
MaxWay Ultra E6 5W-30	TITAN CARGO MAXX SAE 5W-30 XTL	ACEA E9/E7/ E6/E4 API CJ-4 CAT ECF-3	DEUTZ DQC IV-10 LA, DETROIT DIESEL 93K218, MACK EO-O PREMIUM PLUS, MAN M 3271-1 MAN M 3477, MAN M 3575 MAN M 3677, MB-APPROVAL 228.31, MB-APPROVAL 228.51 MTU DDC TYPE 2.1, MTU DDC TYPE 3.1, RENAULT RLD-3, SCA- NIA LA, VOLVO VDS-4.	CUMMINS CES 20081, IVECO 18-1804 CLASSE TLS E6.
MaxWay Ultra E6 10W-40	TITAN CARGO MAXX SAE 10W-40 XTL	ACEA E9/E7/ E6/E4 API CJ-4 JASO DH-2 CAT ECF-3	DETROIT DIESEL 93K218, DEUTZ DQC IV-10 LA, MACK EO-O PREMIUM PLUS, MAN M 3271-1, MAN M 3477, MAN M 3575, MB-APPROVAL 228.31, MB-APPROVAL 228.51, MTU DDC TYPE 2.1, MTU DDC TYPE 3.1, RENAULT RLD-3, SCANIA LA, VOLVO VDS-4.	CUMMINS CES 20081, IVECO 18-1804 CLASSE TLS E9, IVECO 18-1809 CLASSE NG2, VOITH-RETARDER „B“.
PowerWay 15W-40 (ikke 4L)	TITAN UNIVERSAL HD SAE 15W-40	ACEA A3/B3/B4 API SL	DEUTZ DQC I-02, MB-APPROVAL 228.1, MB-APPROVAL 229.1, MTU DDC TYPE 2.	ACEA E2, API CG-4/CF, MIL-L-2104 E, ALLISON C-4, CASE MS 1120, MACK EO-L, MAN 271, NH 330G, STEYR A-202, VOLVO VDS, VW 501 01/505 00.

