



REV.	DESCRIPTION	DATE
A		2019-06-03
B		




Pin Assignment

Cable Specifications:



Test Standard:

- 100% pass open circuit, short circuit, dislocation test
- On-resistance: 3Ω Max.
- Insulation resistance: 5MB Ω Min/DC300V/10ms
- 100% pass 4K @30Hz TV test



Item No.	Length
11.04.5930	1000 ± 30mm
11.04.5931	1500 ± 30mm
11.04.5932	2000 ± 30mm
11.04.5933	3000 ± 30mm

BOM LIST

NO.	SPECIFICATIONS	M	KG	KG	PCS	PCS
1	HDMI 30AWG (1/0.25Cu*1P+1/0.25Cu+AL)*5+1/0.25Cu*4C+AL+D1/0.25Cu+64AM+TPE	M				
2	TPE Black 45P RoHS 2.0 / REACH	KG				
3	HDMI 19 Pin 24K Gold Plated Connector	KG				
4	Dust Cap	PCS				

Item No.	11.04.5930, 11.04.5931, 11.04.5932, 11.04.5933			
ROLINE HDMI High Speed + Ethernet Cable Flexible TPE, M/M, black			Drawer	Ming
Material TPE SCALE			Approved	
REV.	A	UNIT	mm	
Drawing No.				

