

Product information

61 01 200

Bolt End Cutting Nipper

High lever transmission



- Powerful, compact, comfortable
- Better handling, greater capacity and lower handforce required compared to conventional bolt end cutting nippers
- With cutting edges for soft, hard and piano wire
- Particularly high cutting capacity with minimum effort due to optimum transmission ratio
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Forged
- Vanadium electric steel, forged, multi stage oil-hardened



General	
Article No.	61 01 200
EAN	4003773033172
Pliers	black atramentized
Head	polished
Handles	plastic coated
Weight	435 g
Dimensions	200 x 45 x 15 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Cutting capacities soft wire (diameter)	Ø 1 – 6 mm
Cutting capacities medium hard wire (diameter)	Ø 4.0 mm
Cutting capacities hard wire (diameter)	Ø 3.5 mm
Cutting capacities piano wire (diameter)	Ø 3.0 mm

technical change and errors excepted



Almost flush cutting of bolts, nails etc.

