

FPG



Article Number: 251-10709

Grommet, Panel Thickness 0.319"-0.382", PE, Natural, 82ft/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number	FPG
Type	G51PG
Color	Natural (NA)
Features and Benefits	<ul style="list-style-type: none"> • Can be cut to length with scissors, eliminating waste and keeping stock to a minimum. • Available in 9 sizes, for thicknesses from .016" to .512", insuring proper fit.
Product Description	HellermannTyton's Flexiform grommet is a unique, continuous wire protection product which fits easily in all shapes and sizes of holes without the aid of tools or adhesives. Flexiform grommet can be used on any type of material including wood, steel, aluminum, plexiglass, and glass.
Short Description	Grommet, Panel Thickness 0.319"-0.382", PE, Natural, 82ft/pkg

Product Dimensions

Length L (Imperial)	82.0 ft
Reel Length (imperial)	9.7 ft
Variant	Open
Width W (Imperial)	0.52 "
Width W (Metric)	13.2 mm
Width W2 (Imperial)	0.398 "
Width W2 (Metric)	10.1 mm
Height H (Imperial)	0.268 "
Height H (Metric)	6.8 mm
Height H2 (Imperial)	0.189 "
Height H2 (Metric)	4.8 mm
Panel Thickness Max. (Imperial)	0.382 "
Panel Thickness Max. (Metric)	9.70 mm
Panel Thickness Min. (Imperial)	0.319 "
Panel Thickness Min. (Metric)	8.10 mm

Logistics and Packaging

Quantity Per	reel
Package Quantity	82.0 ft
Package Quantity (Metric)	25 m
Carton Quantity	1 Reel
Weight (Metric)	0.99 kg

Material and Specifications

Material	Polyethylene (PE)
Material Shortcut	PE
Flammability	UL94 HB
Halogenfree	Yes
Operating Temperature	-22°F to +176°F (-30°C to +80°C)
ROHS Compliant	Yes