

Type: Male connector 90° with 2 rows

Termination: Press-fit, solder

Number of contacts: 10, 20

Pitch: 2.54 mm


Operational current: 1.5 A

Packaging: Tray

Standard: IEC 60603-2



Technical Specifications on page 36



Accessories

- Processing tools p. 298
- Coding p. 132



Mating connector / Application:



Type B/3 Female connector (p. 50)



Press-fit - Performance level II • • •




No. of contacts	Contact arrangement	Termination length L 	
		3.4 mm	13 mm
		Part number	
20		101-68014	101-78016

On request

- performance level I + III or customized
- special contact length
- contact arrangement



Solder - Performance level II • • •

No. of contacts	Contact arrangement	Termination length L 		
		3.0 mm angled	3.0 mm straight	13 mm angled
		Part number		
10		101-80004	101-80105	101-80006
20		101-80014	101-80115	101-80016

On request

- performance level I + III or customized
- special contact length
- also in THTR
- Board-Lock p. 131
- contact arrangement