

TA241911



Sample image

Order symbol : TA241911

Product nr : 5814002

Description : Enclosure, ABS


Remarks : Grey cover

EAN : 6418074060747


El. number :

- Finland : 3435686
- Denmark : 8212035043
- Sweden : 5814002

Including : Base with PUR gasket and screws for mounting plate/DIN-rail. cover with polyamide cover screws and plastic hinges.



2xM20 knock out



Dimensions :

	Height	Width	Depth
mm :	240	191	107
inch :	9.45	7.52	4.21

Materials :

Material : ABS

Temperatures :

Temperature °C (continuous) :	-40 ... 60
Temperature °F (continuous) :	-40 ... 140

Accessories :

MP 2419	Mounting plate, for enclosures: (210 x 160 x 1)
EKV 12	DIN-35 Mounting rail, for enclosures: (160 x 35 x 7)
DR 210	DIN-35 Mounting rail, for enclosures: (210 x 35 x 7)
FP 10674	Wall fastening lug (2 pcs) incl. screws (40 x 88 x 14)

Ratings :

Ingress protection (EN 60529):	IP65;
Impact Resistance (EN 62262):	IK07;
electrical_insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815) :	Yes
UV resistance :	-
Flammability Rating :	UL 94 HB
Glow Wire Test (IEC 695-2-1) °C :	650C

Certificates :

Certificate FI 40343