

## Profile Recess 20

Profile Recess 20 EF/U7 2m anodised

0022596



### Product features

- A recessed 2000mm length anodised aluminium lighting profile that can be combined with slide (0022618) or click (0022619) opal diffusers with a maximum LED strip width of 20mm and two mounting options (clips or plates). Additional accessories like end caps, profile holders or mounting brackets need to be ordered separately.



## PRODUCT OVERVIEW

Product name	Profile Recess 20 EF/U7 2m anodised
Technology	Accessory
Housing	Aluminium
General application	Retail
ETIM Class	EC002557
E-number FI	4278022
Warranty	3 years
Housing colour	Silver
Product EAN number	5410288225968

## DATA TABLE

### General data

Product name	Profile Recess 20 EF/U7 2m anodised
Technology	Accessory
Housing	Aluminium
General application	Retail
ETIM Class	EC002557
E-number FI	4278022
Warranty	3 years

### Physical data

Housing colour	Silver
Nominal Product Length (mm)	2000
Nominal Product Width (mm)	30
Nominal Product Height (mm)	20.4
Weight (kg)	0.42

### Packaging

Single packaging type	Carton
Product EAN number	5410288225968
Packaging single length / height (cm)	200.0

## Profile Recess 20

*Profile Recess 20 EF/U7 2m anodised*

0022596

Packaging single width (cm)	2.0
Packaging single depth (cm)	2.0
DUN14 (outer)	05410288225968
Units per outer package	35
Packaging outer length / height (cm)	205.0
Packaging outer width (cm)	16.0
Packaging outer depth (cm)	16.0

## TECHNICAL DRAWINGS

