## shrink-fit extensions with IC

with straight shank



## Application

For extending and reducing to smaller diameters.

## Version

- With 4.5 ° angle
- Clamping diameter for shaft tolerance h 6
- Workpiece stop screw with 10 mm adjustment travel

Art. No.	23431 642
Clamping diameter	6 mm
Outer diameter	32 mm
Tapered diameter	20 mm
Length	150 mm
Max. clamp in depth	36 mm
Min. clamp in depth	26 mm
Max. adjustment travel	10 mm
Setting screw size	M5
Width across flats	2.5 mm

## **EAN-Code**

4050293418231

