

## Tipping containers, manual tipping - mobile container with Totalstop brakes

Carrying capacity: up to 800 kg

### Application:

For the collection and disposal of all types of bulk goods and solid materials with floor-level emptying option.

### Version:

- Skip with sliding handle
- Robust sheet steel construction, double-folded top rim, double-folded dumping edge
- 2 steering and 2 fixed castors, 200 x 40 mm TPE wheels, hubs with grooved ball bearings, Totalstop braking system
- No link chain slide guard (see no. 50266034)

### Advantage:

- Totalstop brake system for ideal locking of container for tipping
- With floor-level emptying option



<b>Art. no.</b>	<b>50266 012</b>
<b>Volume</b>	0.45 m <sup>3</sup>
<b>Length</b>	1374 mm
<b>Width</b>	730 mm
<b>Tipper edge height</b>	733 mm
<b>Height</b>	1072 mm
<b>Fork pocket clearance</b>	203 mm
<b>Fork pocket size (W x H)</b>	194 x 72 mm
<b>Number of wheels</b>	4
<b>With drain valve</b>	No
<b>With stacker seat tilt function</b>	No
<b>With wheel lock</b>	Totalstop
<b>With perforated sheet</b>	No
<b>Load-carrying capacity</b>	750 kg
<b>Surface</b>	Powder-coated
<b>Colour</b>	Anthracite grey RAL 7016

### EAN-Code

4017976246987