

## Basic air compressor 250-24 W

boiler size: 24 L, oil-lubricated piston compressor

**metabo**<sup>®</sup>

### Execution:

- for single-phase alternating current
- oil-lubricated piston compressor
- pressure reducer with manometer for controllable working pressure
- additional manometer for displaying tank pressure
- rubberised, robust wheels and handle for mobile applications

### Advantage:

- pressure switch with starter valve for reliable cold start
- 10-year boiler warranty against rust penetration
- no testing necessary before commissioning

### Delivery:

universal quick-release coupling



|   |                    |
|---|--------------------|
| <b>Art. no.</b>   | <b>75290 312</b>   |
| <b>Brand</b>  | METABO             |
| <b>Manufacturer Part Number</b>                         | 601533000          |
| <b>Model</b>  | Basic 250-24 W     |
| <b>Operating pressure</b>                               | 8 bar              |
| <b>Intake air capacity</b>                              | 200 l/min          |
| <b>Delivery quantity effective at 80% max. pressure</b> | 95 l/min           |
| <b>Filling capacity</b>                                 | 110 l/min          |
| <b>Tank capacity</b>                                    | 24 l               |
| <b>Power input</b>                                      | 1500 W             |
| <b>Max. rotation speed</b>                              | 2850 rpm           |
| <b>Sound-pressure level</b>                             | 97 dB              |
| <b>Length x width x height</b>                          | 630 x 406 x 630 mm |
| <b>Weight</b>   | 27 kg              |
| <b>With overload protection</b>                         | Yes                |
| <b>Gross Weight</b>                                     | 26.000 kg          |
| <b>Product Group</b>                                    | 745                |

### EAN

4007430244420