

MODLINK MSDD SOCKET INSERT FRANCE

250VAC/16A orange

France (UTE-NF) orange
for installing in front of main switch
Spring clamp terminals

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC000020
customs tariff number	85366990
GTIN	4048879038157
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	33 mm

Environmental characteristics | Climatic

Storage temperature min.	-10 °C
Storage temperature max.	60 °C

France (UTE-NF)

Connection cross section max.	2,5 mm ²
-------------------------------	---------------------

AWG number max.	14
Operating voltage AC	250 V
Operating current min.	10 A
Operating current max.	16 A
Connection	Spring clamp terminals FK
No. of poles	2 + PE
Connections per pole	2
Protection contact present	yes