






REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE



NOTES:

- 1.DIMENSION SHALL BE INTERPRETED PER ASME Y14.5-2009.
- 1.THICKNESS: 5.2MM
- 2.OPERATION TEMPERATURES: -40℃~+105℃
- 3.WIRE RANGE: 24~12AWG , 0.2~2.5MM²
- 4.MAX.TORQUE VALUE: M3.0 ,5.1KGF.CM
- 5.UNDIMENSIONED TOLERANCES:

PITCH RANGE IN MM		NOMINAL DIMENSION RANGE IN MM							-
TO	OVER	OVER		OVER	OVER	OVER		∅	
6	6 TO 10	10 TO 24	TO 30	30 TO 60	60 TO 100	100 TO 150	OVER 150	□	
±0.10	±0.15	±0.25	±0.20	±0.30	±0.50	±0.70	±1.00	0.05/10	

ITEM	NAME OF PART	NO. OF PART	Q"TY	MATERIAL	NOTES
3	PC2.5-PE-Ground contact	6015B00010(H)	1		
2	PC2.5-PE-Housing	6015A0801A(H)	1	PA66	UL94V-0
1	PC2.5-PE-Housing	6015A0401A(H)	1	PA66	UL94V-0

DETAILED LISTS		MM (INCH)	MATERIAL:				
TOLERANCES EXCEPT AS NOTED		FINISH:	PART NO.:				
.X ±	.X' ±			PC2.5-PE-01P-1Y-00A (H)			
.XX ±	.XX' ±						
.XXX ±	.XXX' ±						
ANGLES ± 1'		APPD:	TITLE: ASSEMBLY DRAWING		REV	T5	
THIRD ANGLE PROJECTION		CHKD:	DRAWING NO.: PC2.5-PE-E01		SCALE	1/1	
		DRFT: LM 11/16/05"	DO NOT SCALE DRAWING		N/A		