



MBU 1


Industrial Connectors:Measuring and Testing Equipment:Sockets:2 mm system

Product description

Description 2 mm diameter bright metal miniature socket. Brass nickel-plated socket body, tin-plated copper beryllium contact (spring-loaded), with solder connection. Suitable for installation in equipment chassis and switch panels up to a maximum wall thickness of 8 mm.

Type MBU 1
Order No. 930 312-000
System 2 mm system

Drawing



Technical data

Type of contact socket (spring-loaded)
Type of termination solder
Rated voltage DC 60 V
Rated current 6 A
Contact resistance 6 mOhm
Mounting screw

Material

Contact material copper beryllium
Contact surface material tin-plated
Housing material PF2400

Environmental conditions

Temperature range -20 °C to +60 °C

Inflammability class

Housing 94 V-0