


Graduated Cylinders - Glass, Class-B with Hexagonal base

CH0345A10-WT



Capacity	10 ml
Sub. Division (ml)	0.2 ml
Tolerance	± 0.20 ml
Overall Height (H)	140 mm
Outer Dia. (D)	16 mm
Max. recommended temperature	250°C

- Class-B graduated cylinder with hexagonal base and spout
- Made of borosilicate glass 3.3
- Meets ISO 4788 standard
- Uniform wall thickness no wedge errors
- Chemical resistant white printing