

PICCOLO PC M 95 G



Sample photo

Order symbol: PC M 95 G
Product nbr: 8724318
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074002310
El. number:
 Finland: 3423419
 Electric No. 8212001763
 Denmark:
 Electric No. Italy: 7201060
 Electric No. Sweden: 2536829

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	230	140	95	CHM-3	DIN-35 Mounting rail
inch:	9.1	5.5	3.7	FM-3	DIN-35 Mounting rail
				FP 22046	Wall fastening lug (4 pcs)

Materials:		Rating:
Material:	Polycarbonate	Ingress Protection (EN 60529): IP66/IP67
Base colour:	RAL 7035 -light grey	Impact Resistance (EN 62262): IK08
Cover screws material:	Polyamide	Electrical insulation: Totally insulated
Cover colour:	RAL 7035 -light grey	Halogen free (DIN/VDE 0472, Part 815): 1
Cover screws colour:	Grey	UV resistance: UL 508
Gasket material:	Polyurethane	Flammability Rating: UL 746C 5"
		Glow Wire Test (IEC 695-2-1) °C: 960
		NEMA Class: NEMA 1, 4X, 6, 12, 13

Temperatures:		Certificates:
Temperature °C (short term):	-40 ... 120 °C	Germanischer Lloyd (GL)
Temperature °C (continuous):	-40 ... 80 °C	SGS Fimko
Temperature °F (short term):	-40 ... 250 °F	Gost R
Temperature °F (continuous):	-40 ... 175 °F	

Accessories:	
M-MP	Mounting plate

