

## Han 16B cover plastic/DL/HBM, HSM, HCC



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 016 5405
Specification	Han 16B cover plastic/DL/HBM, HSM, HCC
HARTING eCatalogue	<a href="https://b2b.harting.com/09300165405">https://b2b.harting.com/09300165405</a>

### Identification

Category	Accessories
Series of hoods/housings	Han <sup>®</sup> B
Type of hood/housing	Protection cover
Description of hood/housing	for bulkhead mounted housings for surface mounted housings Thermoplastic

### Version

Size	16 B
Locking type	Double locking lever

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	10
Net weight	25 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140046450
eCl@ss	27440208 Cap for industrial connectors