

Product information

95 36 320

Cable Cutter

(ratchet principle, 3-stage)

IEC 60900 DIN EN 60900



☆1000V /////

- Sturdy. Easy to use. Stable.
- Innovative ratchet-drive.
- For cable up to Ø 60 mm
- Fixed handle with support area for putting down the pliers when cutting
- Easy handling due to low weight (825 g) and compact construction (320 mm length) - also usable in confined areas
- Cutting through copper and aluminium cables up to Ø 60 mm in onehand and two-hand operation
- Hardened, precision-ground cutting edges cut smoothly and neatly without crushing
- For cutting copper and aluminium single conductors as well as multiple stranded cables
- Innovative three-stage ratchet-drive with high leverage for easy cutting in one-hand and two-hand operation
- Not suitable for steel wire, wire ropes and fine-stranded (highly flexible) conductors
- High-grade special tool steel, forged, oil-hardened

General	
Article No.	95 36 320
EAN	4003773075189
Pliers	black atramentized
Head	polished
Handles	insulated with multi-component grips, VDE-tested
Weight	830 g
Dimensions	320 x 188 x 39 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Cutting capacity copper cable, multiple- stranded	600 mm ²
Cutting capacity copper cable, multiple- stranded	Ø 60 mm
MCM	1,200
VDE tested	yes

technical change and errors excepted

KNIPEX Quality – Made in Germany









