

Electronic 3-point internal micrometer

Micromar 44 EWR, carbide-tipped measuring surfaces



Application:

For measuring through holes and blind bores and short centring shoulders in series.

Execution:

- Self-centring and self-aligning
- Carbide-tipped measuring faces
- Locking function
- Zero setting at any position
- mm/inch changeover
- ABS function
- Preset function

Delivery:

Single device with battery (1 x 3 V lithium, type CR 2032) and operating instructions in a case



| | |
|---|-------------------|
| Art. no. | 31912 030 |
| Brand | MAHR |
| Manufacturer Part Number | 4191127 |
| Min./max. length measuring range | 30-40 mm |
| Measuring depth | 76 mm |
| Data transmission type | multiCOM |
| Digit increment | 0.001 mm |
| IP protection class | IP 52 |
| Error limit | 0.004 mm |
| Display | Digital |
| Number of rechargeable batteries/batteries | 1 PCS |
| Battery designation | 3V CR2032 Lithium |
| DIN | 863 |
| Calibration Group | I |
| Gross Weight | 1.243 kg |
| Product Group | 305 |

EAN

4059192010966