


PRODUCT SPECIFICATION

Brand	C.K
Product Range	Step & Cone Drills
Catalogue number	3008, 3010, 3011, 3012, 3013, 3014, 3015
Date	05/02/2015

<p>Range Description A range of Step and cone drills</p> <p>Features</p> <ul style="list-style-type: none"> • HSS construction • Self starting tip • Dual flute construction for less drilling pressure, faster drilling and longer tool life • Three flats on drive shaft for secure drive in drill chucks 	
---	--

Item Number	Item Description	EAN No	Commodity code	Carton Qty
T3008	HSS-Multi-Step drill 6, 9, 12.5, 15.2, 18.6, 20.4, 22.5, 25.5, 28.3 & 30.5mm (PG7, PG9, PG11, PG13, PG16, M25, PG21)	5013969985283	82075060	5
T3010 1	HSS Multi-Step drill 4, 6, 8, 10, 12, 14, 16, 18 & 20mm Diameters	5013969985313	82075060	10
T3011	HSS Multi-Step drill 6, 8, 10, 12, 14, 16, 18, 20, 22, 24, 26, 28, 30 & 32mm	5013969977608	82075060	5
T3012	HSS Multi-Step drill 12.5, 12.7, 15.2, 16.2	5013969978056	82075060	5

	18.6, 20.4, 22.5, 25.4, 28.3, 30.5, 32.5 & 32.5mm			
T3013	HSS TiN Multi-Step drill 6, 8, 10, 12, 14, 16, 18, 20, 22, 24, 26, 28, 30 & 32mm	5013969978063	82075060	5
T3014	High Speed Steel Cone Drill 6 - 26mm	5013969978070	82075060	5
T3015	High Speed Steel Cone Drill 16 - 32mm	5013969978087	82075060	5

Technical product information	
Standards compliance	
User health and safety information	None applicable
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K Step & Cone drills are guaranteed for life against imperfect materials or workmanship Normal wear & tear or damage caused through inappropriate work is not covered
Country of origin	Taiwan

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T3008	31	31	95	146	35	35	115	191
T3010 1	20	20	70	50	25	25	105	61
T3011	31	31	95	141	35	35	115	186
T3012	33	33	115	130	45	45	125	175
T3013	32	32	115	130	45	45	125	175
T3014	26	26	95	71	45	45	115	116
T3015	32	32	115	130	45	45	125	175

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T3008	150	120	90	1018		
T3010 1	150	110	70	660		
T3011	150	120	90	993		
T3012	150	120	90	938		
T3013	150	120	90	938		

T3014	150	120	90	643		
T3015	150	120	90	938		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T3008	45	Tube					63	Box
T3010 1	11	Tube					50	Box
T3011	45	Tube					63	Box
T3012	45	Tube					63	Box
T3013	45	Tube					63	Box
T3014	45	Tube					63	Box
T3015	45	Tube					63	Box