

Temperature data logger

testo 175 T3


- Large, easy-to-read display
- Measurement data memory for 1 million readings
- Up to 3 years of battery life
- Data transfer via USB cable or SD card
- Two external sensor connections type T and type K




	Type T (Cu-CuNi)	Type K (NiCr-Ni)
Measuring range	-50 to +400 °C	-50 to +1000 °C
Accuracy ±1 digit	±0.5 °C (-50 to +70 °C) ±0.7% of m.v. (+70.1 to +1000 °C)	
Resolution	0.1 °C	

testo 175 T3

2-channel temperature data logger with external sensor connections (TC type T and type K) including wall bracket, lock, batteries and calibration protocol

Order no. 0572 1753



Probe type	Dimensions Probe shaft/probe shaft tip	Measuring range	Accuracy	t ₉₉	Order no.
Magnetic probe, adhesive power approx. 20 N, with magnets, for measurements on metal surfaces, TC type K, fixed cable		-50 to +170 °C	Class 2 ¹⁾	150 s	0602 4792
Pipe wrap probe for pipe diameter 5 to 65 mm, with interchangeable measuring head, TC type K, fixed cable 1.2 m		-60 to +130 °C Short-term measuring range up to +280 °C	Class 2 ¹⁾	5 s	0602 4592
Clamp probe for measurements on pipes, pipe diameters 15 to 25 mm (max. 1"), TC type K, fixed cable		-50 to +100 °C Short-term measuring range up to +130 °C	Class 2 ¹⁾	5 s	0602 4692

1) According to standard EN 60584-2, the accuracy of Class 1 refers to -40 to +1000 °C (type K), Class 2 to -40 to +1200 °C (type K), Class 3 to -200 to +40 °C (type K).
2) According to standard EN 60584-2, the accuracy of Class 1 refers to -40 to +350 °C (type T).

USB data logger

Temperature **testo 184**

- Clear alarm indication
- Very easy to operate
- Very easy configuration with no software installation
- Convenient readout thanks to automatic PDF report
- Mobiles readout possible via NFC
- IT-safe (no installation, no download)

Measuring range	-35 to +70 °C
Accuracy	±0.5 °C
Resolution	0.1 °C

testo 184 T3

Unlimited operating time thanks to exchangeable battery

Available in packs of 1, 10 and 50 off

Order no. 0572 1843



Accessories for testo 184 T3

Order no.

Mobile printer for data loggers testo 175/176/184	0572 0576
ComSoft Professional, professional software, including data archiving	0554 1704
Wall bracket for testo 184	0554 1841
Lithium battery CR2450, 3 V	0515 5841