

Shielding efficiency	70 dB
Cable type	coaxial cable
Inner conductor material	CCS
Inner conductor, core diameter	0.5
Number of shieldings	2 x
Type 1, shielding	foil (aluminium)
Type 2, shielding	braid (aluminium) 32x
Material cable sheath	PVC
Cable sheath diameter (approx.)	5 mm


Goobay

Angled antenna cable (<70 dB), 2x shielded

Coaxial male > Coaxial female 90°

- double shielded coaxial cable
- encapsulated unshielded plug on both sides, protection against dust, dirt and mechanical loads
- nickel plated contacts

1.50 m	11712	Bulk
5.00 m	11714	Bulk
10.00 m	51254	Bulk



Shielding efficiency	70 dB
Cable type	coaxial cable
Inner conductor material	CCS
Inner conductor, core diameter	0.5
Number of shieldings	2 x
Type 1, shielding	foil (aluminium)
Type 2, shielding	braid (aluminium) 32x
Material cable sheath	PVC
Cable sheath diameter (approx.)	5 mm


Goobay

Angled antenna cable (<70 dB), 2x shielded

Coaxial male 90° > Coaxial female 90°

- double shielded coaxial cable
- encapsulated unshielded plug on both sides, protection against dust, dirt and mechanical loads
- nickel plated contacts

1.50 m	11520	Bulk
2.50 m	11521	Bulk
5.00 m	11522	Bulk
10.00 m	11524	Bulk



Shielding efficiency	70 dB
Cable type	coaxial cable
Inner conductor material	CCS
Inner conductor, core diameter	0.5
Number of shieldings	2 x
Type 1, shielding	foil (aluminium)
Type 2, shielding	braid (aluminium) 32x
Material cable sheath	PVC
Cable sheath diameter (approx.)	5 mm

Goobay

Angled antenna cable (<70 dB), 2x shielded

Coaxial male 90° > Coaxial female 90°

- double shielded coaxial cable
- encapsulated unshielded plug on both sides, protection against dust, dirt and mechanical loads
- nickel plated contacts

1.50 m	11525	Bulk
2.50 m	11526	Bulk
5.00 m	11527	Bulk
10.00 m	11566	Bulk

