

Within Series Adaptor 32_SMA-50-0-52/199_N

Description

Adaptor plug/plug
SMA plug (male) / SMA plug (male)

Interface standard
Series SMA - IEC 60169-15_MIL-STD-348A/310_CECC 22110



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz
VSWR	DC - 18 GHz ≤ 1.05 + 0.005 f (GHz)
Electrical length	23.2 mm

Mechanical Data

Number of matings	500
Weight	0.0052 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS)	compliant

Material Data

Interface - SMA plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	Passivated (Plating)
Body	Stainless Steel	Passivated (Plating)
Insulator	PFA / PTFE	
Coupling nut	Stainless Steel	Passivated (Plating)
Gasket	VMQ (Silicone rubber)	

Interface - SMA plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	Passivated (Plating)
Body	Stainless Steel	Passivated (Plating)
Insulator	PFA / PTFE	
Coupling nut	Stainless Steel	Passivated (Plating)
Gasket	VMQ (Silicone rubber)	

Related Documents

Catalogue drawing	DCA-00013692
-------------------	--------------

Ordering Information

Single package	32_SMA-50-0-52/199_NE
----------------	-----------------------

Within Series Adaptor 32_SMA-50-0-52/199_N