



24P3CW

23.8 inch (60.5 cm) LCD MONITOR

23.8" FHD 3-sided flat IPS display for easy productivity in any office setting

General

Model name	24P3CW
EAN	4038986140812
Product Line	Pro-line
Series	P3
Channel	B2B
Classification	Mainstream
Section	Business
Launch date	2023-02-14T11:36:14+00:00
Continent	Europe
Product status (EU)	Launch

Screen

Resolution	1920x1080
Refresh rate	75Hz
Screen size (inch)	23.8 inch
Screen size (cm)	60.5 cm
Flat / Curved	Flat
Backlight	WLED
Panel Type	IPS
Aspect ratio	16:9
Display Colours	16.7 Million
Panel Colour in Bits	8
Pixel Pitch	0.2745
Pixels per Inch	93
Response time (GtG)	4 ms
Contrast (static)	1000:1
Contrast (dynamic)	20M:1
Brightness (typical)	300 cd/m ²
Viewing angle (CR10)	178/178 °
Hard Glass	Antiglare + 3H
OSD languages	EN, FR, ES, PT, DE, IT, NL, SE, FI, PL, CZ, RU, KR, CN (T), CN (S), JP

Exterior

Monitor colour	Black
Bezel Type	3-sided frameless
Removable Stand	✓
Cable Management System	✓

Ergonomics

Vesa Wallmount	100x100
Tilt	-5~35° °
Swivel	-180/180 °
Pivot	✓
Height Adjust Amount	150mm

Connectivity and Multimedia

Signal Input	HDMI 1.4 x 1, DisplayPort 1.2 x 2, USB-C (DP Alt Mode)
USB-C Features	DP alt mode, Data Transfer (USB upstream), Power Delivery 65W
USB input	USB 3.2 (Gen1) x 4
USB Hub	✓
USB out ports	4
USB fast charge	✓
RJ-45	✓
Displayport output	✓

Multimedia

Built-in Speakers	5 W x 2
Audio output	Headphone out (3,5mm)
Microphone	✓
Webcam	5MP Windows Hello

Features

Sync Technology	AdaptiveSync
Flicker-free	✓
RJ45	✓
Blue Light Technology	Low blue light
Kensington Lock	✓

Power / Environmental

Powersupply	Internal
Powersource	100 - 240V 50/60Hz

Warranty

Warranty Period	3 Years
-----------------	---------

What's in the Box?

HDMI cable	1,8 m
Displayport Cable	1,8 m
USB cable	USB Type-C to C/A m
Power Cable C13	1,8 m