

**SOLID PC 3828 13 T**



Sample photo

**Order symbol:** PC 3828 13 T  
**Product nbr:** 5330063  
**Description:** Enclosure, PC  
**Remarks:** Transparent cover

**EAN:** 6418074005557  
**EI. number:**  
 Finland: 3423817  
 Electric No. Italy: 7402050  
 Electric No. Sweden: 2539452

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

**Dimensions: Length Width Height Accessories:**

Dimensions:	Length	Width	Height	Accessories:	
mm:	378	278	130	EKPXT	Mounting plate isolated
inch:	14.9	10.9	5.1	EKV 22	DIN-35 Mounting rail
<b>Materials:</b>				EKV 32	DIN-35 Mounting rail
Material: Polycarbonate				EKPZR	Extension frame

**Base colour:** RAL 7035 -light grey  
**Cover screws material:** Polyamide  
**Cover colour:** Clear transparent  
**Cover screws colour:** Grey  
**Gasket material:** Polyurethane

**Rating:**

Ingress Protection (EN 60529): IP66/IP67  
 Impact Resistance (EN 62262): IK08/IK09  
 Electrical insulation: Totally insulated  
 Halogen free (DIN/VDE 0472, Part 815): 1  
 UV resistance: UL 508  
 Flammability Rating: UL 746C 5"  
 Glow Wire Test (IEC 695-2-1) °C: 960  
 NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12

**Temperatures:**

**Temperature °C (short term):** -40 ... 120 °C  
**Temperature °C (continuous):** -40 ... 80 °C  
**Temperature °F (short term):** -40 ... 250 °F  
**Temperature °F (continuous):** -40 ... 175 °F

**Certificates:**

SGS Fimko  
 Gost R

**Accessories:**

EKPVT Mounting plate

