


KEMET Part Number: PME271E622KR30
(P277EJ224K300A)

Capacitor, film, 0.22 uF, +/-10% Tol, -40/+110C, Safety: X1, 300 VAC, Lead Spacing=25.4 mm



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	30.5	MAX
H	19	MAX
T	12.1	MAX
S	25.4	+/-0.4
LL	30	+5
F	1	+/-0.05

Packaging Specifications	
Package Kind:	Bulk
Package Quantity:	100

General Information	
Supplier:	KEMET
Dielectric:	Metallized Paper
Application:	Safety: X1
Style:	Radial Molded
Lead Form:	Wire Leads
Approvals:	ENEC,UL
RoHS:	Yes

Specifications	
Capacitance:	0.22 uF
Voltage:	630 VDC
Tolerance:	+/-10%
Voltage AC:	300 VAC
Rated Temperature:	110C
Temperature Range:	-40/+110C
Dissipation Factor @ 1 kHz:	1.3%
Insulation Resistance:	12 GOhm
Maximum dVdT:	400 v/us
Miscellaneous:	SRF= 2.6 MHz