

Weatherproof Connectors

Order code	Manufacturer code	Description
23-1420	n/a	3 POLE + EARTH CABLE PLUG
23-1425	932 510 100	6 POLE + EARTH CABLE PLUG
23-1430	n/a	3 POLE + EARTH CABLE SOCKET
23-1435	932509100	6 POLE + EARTH CABLE SOCKET
23-1440	n/a	3 POLE + EARTH PANEL PLUG
23-1445	n/a	6 POLE + EARTH PANEL PLUG
23-1450	n/a	3 POLE + EARTH PANEL SOCKET
23-1455	932 325 100	6 POLE + EARTH PANEL SOCKET














Weatherproof Connectors	Page 1 of 4
The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 04/07/2003







Technical Specification

No. of Poles	3 + Earth	6 + Earth
Maximum Voltage	DC 250V AC 380V	DC 150V AC 250V
Maximum Current	AC 16A/DC 10A	10A
Contact Resistance	3m Ω	5m Ω
Pin Diagram	2mm	1.5mm
Maximum Wire Size	1.5mm ² /AWG16	0.75mm ² /AWG19
UL Standard	94V - 0	94V - 0
Rating	IP 65	IP 65
Temperature Range	-40°...90°C	-40°...90°C


Part Number	No. of Poles	Cable Clamp Size	Max. Cable Size
CA3LS09	3+ Earth	Pg 9	6-9.5mm
CA3LD09	3+ Earth	Pg 9	6-9.5mm
CA3GS	3+ Earth	N/A	N/A
CA3GD	3+ Earth	N/A	N/A

Part Number	No. of Poles	Cable Clamp Size	Max. Cable Size
CA6LS11	6+ Earth	Pg 11	8-11mm
CA6LD11	6+ Earth	Pg 11	8-11mm
CA6GS	6+ Earth	N/A	N/A
CA6GD	6+ Earth	N/A	N/A





RU 3514



RU 3514

