


## MIRO TR 90-250VAC FK OPTO-COUPLER MODULE


IN: 250 VAC - OUT: 48 VDC / 2 A

Transistor 2 A  
230 V AC  
Spring clamp terminals

### [Link to Product](#)

#### Illustration





Product may differ from Image

### Approvals



### Input

Voltage range ON	90...250 V AC
Voltage range OFF	0...30 V AC
Control current	15 mA
LED display	LED (yellow)

### General data

Test isolation voltage	2.5 kV
Mounting method	DIN-rail mountable (EN 60715)
Housing	Black plastic, flame retardant
Temperature range	-20...+60 °C
Dimensions H × W × D	78×6.2×65 mm

### Output

Switching voltage	5...48 V DC
Switching current per output	1 mA...2 A (without derating)
Saturation voltage (across output)	max. 0.3 V DC
Leakage current (output is open)	max. 0.3 mA
Switching frequency	max. 10/1 Hz (resist./ind.)
Switching time ON/OFF	3/10 ms

### Commercial data

country of origin	CZ
customs tariff number	85414090
minimum order quantity	1