

CTAM10C2



Article Number: 151-31101

Cable Tie Anchor Mount, 0.17" Hole Dia., 0.2" Max Tie Width, PA66, Black, 100/pkg



Download spec sheet

Base Data

Local Order Number	CTAM10C2
Type	CTAM1
Color	Black (BK)
Features and Benefits	<ul style="list-style-type: none"> • 4-way entry allowing the cable tie to secure bundles running parallel or perpendicular. • Secures with a single screw providing quick installation.
Product Description	HellermannTyton cable tie anchor mounts are designed with a 4-way entry allowing the cable tie to secure bundles running parallel or perpendicular. The mounts are installed quick and easy by securing a single screw.
Short Description	Cable Tie Anchor Mount, 0.17" Hole Dia., 0.2" Max Tie Width, PA66, Black, 100/pkg

Product Dimensions

Length L (Imperial)	0.8 "
Length L (Metric)	20.4 mm
Fixation Method	Screw Mounting and Rivet
Width W (Imperial)	0.4 "
Width W (Metric)	10.2 mm
Cable Tie Width Max. (Imperial)	0.2 "
Cable Tie Width Max. (Metric)	5.0 mm
Height H (Imperial)	0.2 "
Height H (Metric)	5.1 mm
Height H2 (Imperial)	0.06 "
Height H2 (Metric)	1.8 mm
Mounting Hole Diameter D (Imperial)	0.17 "
Mounting Hole Diameter D (Metric)	4.3 mm
Mounting Hole Diameter D Max. (Metric)	4.3 mm
Mounting Hole Diameter D Min. (Metric)	4.3 mm

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	100

Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL94 V2

Operating Temperature -40°F to +185°F (-40°C to +85°C)

ROHS Compliant Yes

Certification/Specification UL

UL Listed (US and Canada) No

UL Recognized (US and Canada) Yes