

Product information

95 11 160

KNIPEX StepCut Cable Shears



- Small, light, strong: comfortable cutting without crushing and just 160 mm in size
- Noticeably less effort: the gradations cut wires one after the other; cutting is up to 40% easier than with standard cable shears of the same length!
- Ergonomic handle design: optimal cutting feel even for larger cable diameters
- Cuts multi-core stranded copper and aluminium cables up to Ø 15 mm (50 mm²)
- Cuts solid copper and aluminium cables up to 5 x 4 mm²
- Cuts without crushing
- Bolted joint: precise, effortless, durable
- Pinch guard fitted for safe work
- Not suitable for steel wire and hard drawn copper conductors
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 56 HRC
- High-grade special tool steel, forged, oil-hardened



General	
Article No.	95 11 160
EAN	4003773085904
Shears	burnished
Handles	plastic coated
Weight	180 g
Dimensions	160 x 40 x 14 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Cutting capacity copper cable, multiple-stranded	50 mm ²
Cutting capacity copper cable, multiple-stranded	Ø 15 mm
AWG	1 / 0

technical change and errors excepted



