

Product information

95 36 315 A

Cable Cutter

(ratchet action)

For steel wire armoured cables (SWA cable)

IEC 60900 DIN EN 60900

- Cuts through steel wire armoured cables up to Ø 45 mm / 380 mm² (e.g. 4 x 95 mm²) using one or two-handed operation
- Sturdy. Easy to use. Stable.
- Simple handling due to low weight (800 g) and compact design (315 mm length) - can also be used in confined areas
- Precision-ground blades and induction-hardened cutting edges cut smoothly and neatly without crushing
- Innovative high leverage three-stage ratchet-drive
- Support area for putting down the pliers when cutting Not suitable for cutting ACSR cable and wire rope!
- Cutter head: special high-grade tool steel, forged, oil-hardened



☆1000V ///// ③

General	
Article No.	95 36 315 A
EAN	4003773078579
Pliers	black lacquered
Handles	insulated with multi-component grips, VDE-tested
Weight	800 g
Dimensions	315 x 140 x 30 mm
Standard	IEC 60900 DIN EN 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Cutting capacity copper cable, multiple-stranded	380 mm ²
Cutting capacity copper cable, multiple- stranded	Ø 45 mm
MCM	750
VDE tested	yes

technical change and errors excepted

KNIPEX Quality – Made in Germany







Precision-milled and induction-hardened cutting edge