

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0834229018](#)
Status: **Active**
Overview: Commercial Micro-D High-Density Connectors
Description: Commercial Micro-D, CMD Single Ended, 15 Circuits, Female - Pigtail, 1.83m Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-83421-001-001 \(PDF\)](#)

General

| | |
|------------------------|--|
| Product Family | Cable Assemblies |
| Series | 83422 |
| Assembly Configuration | Single Ended Connector |
| Connector to Connector | Commercial Micro-D-to-Pigtail |
| Overview | Commercial Micro-D High-Density Connectors |
| Product Name | Commercial Micro-D |
| UPC | 800756425375 |


Physical

| | |
|--------------------------------|----------------------|
| Cable Length | 1.83m |
| Circuits (Loaded) | 15 |
| Gender | Female-Pigtail |
| Lock to Mating Part | None |
| Material - Plating Termination | Tin |
| Net Weight | 15.056/g |
| Packaging Type | Bag |
| Plating min - Mating | 0.127µm |
| Plating min - Termination | 1.270µm |
| Single Ended | Yes |
| Termination Interface: Style | Crimp or Compression |
| Wire Insulation Diameter | .225mm (5.720") max. |
| Wire Size AWG | 28 |
| Wire/Cable Type | N/A |

Material Info

Reference - Drawing Numbers

| | |
|-----------------------|------------------|
| Product Specification | PS-83421-001-001 |
| Sales Drawing | SD-83422-9007 |



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[83422 Series](#)