

**RKDG D18 WG PT6****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Intelligent cabling solutions can save you valuable time and money.**

The FieldPower® modular system contains the right solution for every cabling task.

Foldable seals for the use of pre-assembled cables

Seals available with M16 and M20 connection thread

Integration of operating and signalling devices into the

seal possible

**General ordering data**

Version	FieldPower®, Field Power® sealing insert, round, IP54, 18.5 - 20.5 mm
Order No.	<a href="#">2491870000</a>
Type	RKDG D18 WG PT6
GTIN (EAN)	4050118501537
Qty.	10 pc(s).

Creation date May 2, 2022 9:17:48 AM CEST

Catalogue status 22.04.2022 / We reserve the right to make technical changes.

## RKDG D18 WG PT6

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

Depth	18 mm	Depth (inches)	0.709 inch
Height	33.8 mm	Height (inches)	1.331 inch
Width	46.7 mm	Width (inches)	1.839 inch
Net weight	21.8 g		

### Temperatures

Operating temperature	-40 °C...85 °C
-----------------------	----------------

### General data

Clamping range, max.	20.5 mm	Clamping range, min.	18.5 mm
Colour	black	Design	Seal
Line type	round	Material	EPDM
Mounting position, installation notice	in FieldPower® sealing slot	Protection degree	IP54
Silicone	No	UL 94 flammability rating	HB

### Classifications

ETIM 6.0	EC002624	ETIM 7.0	EC002624
ETIM 8.0	EC002624	ECLASS 9.1	27-18-27-90
ECLASS 10.0	27-18-28-15	ECLASS 11.0	27-18-28-15

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>