

DWLN steel boring bar, negative right

For facing and longitudinal turning with WN indexable insert

WIDIA 

Application:

For facing and longitudinal turning with WN indexable insert, 80°

Execution:

- Precision-manufactured steel boring bar, internal cooling, type W, pitch angle 95°, tip angle 80°, clearance angle 0°

Advantage:

- Three-edge geometry lowers cost per cutting edge
- Negative body geometry ensures good stability and absorption of force for large cutting depths



Art. no.	17684 017
Brand	WIDIA
Manufacturer Part Number	5696269
ISO name	A 25 R DWLN R/L 08
Min. bore diameter	32 mm
Shank diameter	25 mm
Length	200 mm
Programming size	17 mm
Suitable for indexable inserts	WN.. 0804..
Tool design	Right
Gross Weight	720.000 g
Product Group	1XG

EAN

4050841471305