

Clamping screw sets



Version:

- Tempered
- Strength class 8 or 10
- Different clamping heights can be set as required using extension nuts and studs (extension studs).
- Widths across flats are in accordance with ISO standard (DIN ISO 272)

Delivery:

In a sturdy, high-quality wooden box with removable hinged lid.



Art. no.	26209 180
Suitable for groove width	18 mm
Thread dimension	M16
Number of DIN 787 T-slot screws	2 x M16 x 63 mm, 4 x M16 x 100 mm
Number of DIN 6379 stud bolts (extension pin)	4 x M16 x 80 mm, 4 x M16 x 125 mm, 4 x M16 x 160 mm
Number of DIN 508 slots	4 PCS
Number of DIN 6330 B high nuts	4 PCS
Number of extension nuts	4 PCS
Wooden box length	339 mm
Wooden box width	294 mm
Wooden box height	48 mm

EAN-Code

4020772083038