

## Folding door cabinet, height 1950 mm

With shelf, load capacity 80 kg per shelf

### Execution:

- Stable, welded steel sheet structure with base
- Galvanised shelves, height-adjustable in increments of 17 mm
- Practical, inset-type folding doors with internal pivot pins, doors reinforced by box-type profile on inside, approx. 125° door opening angle
- Locks by means of turning handle with triple-point security cylinder lock, incl. 2 keys

### Advantage:

- With the folding-door mechanism, more space is provided; ideal for use in narrow passageways or in tight workplaces
- An even better view into the cabinet since large door surfaces no longer block the way

### Delivery:

On request: Load capacity per shelf 100 kg with evenly distributed load, DOM locking system (suitable for HK tool cabinets, HK tool shelves, HK workbenches, HK hinged-door and sliding-door cabinets). Other colours available on request.



<b>Art. no.</b>	<b>50046 426</b>
<b>Brand</b>	PAVOY
<b>Manufacturer Part Number</b>	39393-120-600-7357 16
<b>Door design</b>	Full-sheet panel
<b>Height</b>	1950 mm
<b>Depth</b>	600 mm
<b>Width</b>	1200 mm
<b>Number of shelves</b>	4 PCS
<b>Load-carrying capacity per shelf</b>	80 kg
<b>Number of folder height</b>	5 PCS
<b>Load-carrying capacity</b>	400 kg
<b>With partition wall</b>	No
<b>Lock type</b>	Twist-grip lock with three-point fastening
<b>Material</b>	Sheet steel
<b>Cabinet colour</b>	Light grey RAL 7035
<b>Colour of front</b>	Anthracite grey RAL 7016
<b>Surface</b>	Powder-coated
<b>Gross Weight</b>	89.000 kg
<b>Product Group</b>	5CB