

## Sheet metal punches, Tristar

12.5 to 63 mm



### Application:

For punching holes in sheet metal.

### Execution:

- Sheet hole-punch system with slug splitter for standard steel S235
- Burr-free hole punching
- Actuated using a wrench, hydraulic punch or cordless compact punch
- When actuated with a wrench, draw bolts with ball bearings must be used

### Advantage:

- The sheet does not jam in the centre thanks to the triple partition

### Delivery:

Stamp and die – screw or tension bolt has to be ordered separately



<b>Art. no.</b>	<b>53829 505</b>
<b>Brand</b>	ALFRA
<b>Manufacturer Part Number</b>	01784
<b>Diameter</b>	50.5 mm
<b>Suitable for max. sheet metal thickness</b>	3 mm
<b>Screw diameter</b>	19 mm
<b>Screw length</b>	75 mm
<b>Gross Weight</b>	0.655 kg
<b>Product Group</b>	554

### EAN

4030266122815